

ČERPADLA PRO DŮM A ZAHRADU - letáková cena 06/2026

Objednáací číslo	Výrobek	Letáková cena v Kč bez DPH	Letáková cena v Kč s DPH CZ	Letáková cena v EUR bez DPH	Letáková cena v EUR s DPH SK
92712331	SB 3-35 M s 15m kabelem	12 408,05 Kč	15 013,74 Kč	496,32 €	610,48 €
92712333	SB 3-35 A s 15m kabelem	12 852,25 Kč	15 551,22 Kč	514,09 €	632,33 €
92712338	SB 3-45 M s 15m kabelem	13 676,54 Kč	16 548,61 Kč	547,06 €	672,89 €
92712340	SB 3-45 A s 15m kabelem	14 183,62 Kč	17 162,18 Kč	567,34 €	697,83 €
92713049	SBA 3-35 M s 15m kabelem	14 902,42 Kč	18 031,93 Kč	596,10 €	733,20 €
92713060	SBA 3-35 A s 15m kabelem	16 403,14 Kč	19 847,80 Kč	656,13 €	807,03 €
92834170	SBA 3-45 M s 15m kabelem	16 255,34 Kč	19 668,96 Kč	650,21 €	799,76 €
92713068	SBA 3-45 A s 15m kabelem	17 270,03 Kč	20 896,74 Kč	690,80 €	849,69 €
92713100	SBA 3-45 MW s 15m kabelem	19 172,56 Kč	23 198,80 Kč	766,90 €	943,29 €
92713101	SBA 3-45 AW s 15m kabelem	20 398,46 Kč	24 682,14 Kč	815,94 €	1 003,60 €
99432876	Hydro Solo E CRIE 5-7 1x220-240V 50Hz	83 157,50 Kč	100 620,58 Kč	3 326,30 €	4 091,35 €
99530405	SCALA1 3-45	13 392,41 Kč	16 204,82 Kč	535,70 €	658,91 €
99530407	SCALA1 5-55	16 088,00 Kč	19 466,48 Kč	643,52 €	791,53 €
93013252	SCALA2 3-45	18 580,67 Kč	22 482,61 Kč	743,23 €	914,17 €
93225672	Tlaková řídicí jednotka PM Start	2 811,38 Kč	3 401,77 Kč	112,46 €	138,32 €
93264954	Tlaková řídicí jednotka PM Plus	4 291,04 Kč	5 192,16 Kč	171,64 €	211,12 €
99463875	JP 4-47 PT-H 20l	13 739,83 Kč	16 625,19 Kč	549,59 €	676,00 €
99594664	JP 4-47 PT-H 60l	19 268,30 Kč	23 314,64 Kč	770,73 €	948,00 €
99594666	JP 5-48 PT-H 60l	20 873,98 Kč	25 257,52 Kč	834,96 €	1 027,00 €
98374701	CMBE 3-62 1x220-240V 50Hz	36 865,14 Kč	44 606,82 Kč	1 474,61 €	1 813,76 €
99458767	JP 4-47 S - BBVP	9 469,98 Kč	11 458,68 Kč	378,80 €	465,92 €
99458769	JP 5-48 S - BBVP	10 420,97 Kč	12 609,37 Kč	416,84 €	512,71 €
96468354	UNILIFT AP50B.50.08.A1V 1x230V 10m kabel	24 351,04 Kč	29 464,76 Kč	974,04 €	1 198,07 €
96468356	UNILIFT AP35B.50.06.A1V 1x230V 10m kabel	16 339,98 Kč	19 771,38 Kč	653,60 €	803,93 €
96010981	UNILIFT AP12.50.11.A1 1x230V 10m kabel	31 728,26 Kč	38 391,19 Kč	1 269,13 €	1 561,03 €
96011018	UNILIFT AP12.40.04.A1 1x230V 10m kabel	19 087,80 Kč	23 096,24 Kč	763,51 €	939,12 €
011H1800	UNILIFT KP 150A1 1x230V 50Hz 10m kabel	9 659,97 Kč	11 688,56 Kč	386,40 €	475,27 €
011H1900	UNILIFT KP 150 AV1 1x230V 50Hz 10m kabel	10 188,45 Kč	12 328,02 Kč	407,54 €	501,27 €
012H1800	UNILIFT KP 250A1 1x230V 50Hz 10m kabel	11 435,92 Kč	13 837,46 Kč	457,44 €	562,65 €
012H1900	UNILIFT KP 250 AV1 1x230V 50Hz 10m kabel	12 027,75 Kč	14 553,58 Kč	481,11 €	591,77 €
013N1900	UNILIFT KP 350 AV1 1x230V 50Hz 10m kabel	17 016,31 Kč	20 589,74 Kč	680,65 €	837,20 €
96280966	UNILIFT CC5 A1 1x230V 50Hz 5m kabel	5 981,99 Kč	7 238,21 Kč	239,28 €	294,31 €
96280968	UNILIFT CC7 A1 1x230V 50Hz 10m kabel	6 933,44 Kč	8 389,46 Kč	277,34 €	341,13 €
96280970	UNILIFT CC9 A1 1x230V 50Hz 10m kabel	8 983,76 Kč	10 870,35 Kč	359,35 €	442,00 €
92611467	UNILIFT APG.40.10.A1 1x230V	24 879,47 Kč	30 104,16 Kč	995,18 €	1 224,07 €
97775314	Sololift2 WC-1	12 619,60 Kč	15 269,72 Kč	504,78 €	620,88 €
97775315	Sololift2 WC-3	15 304,19 Kč	18 518,07 Kč	612,17 €	752,97 €
97775316	Sololift2 CWC-3	15 853,66 Kč	19 182,93 Kč	634,15 €	780,00 €
97775317	Sololift2 C-3	14 268,32 Kč	17 264,67 Kč	570,73 €	702,00 €
97775318	Sololift2 D-2	11 308,95 Kč	13 683,83 Kč	452,36 €	556,40 €
97936156	Conlift 1	3 064,86 Kč	3 708,48 Kč	122,59 €	150,79 €
97901037	Multilift MSS.11.1.2 1X230V 50Hz	49 653,81 Kč	60 081,11 Kč	1 986,15 €	2 442,97 €

ČERPADLA PRO DŮM A ZAHRADU - letáková cena 06/2026

Objednací číslo	Výrobek	Letáková cena v Kč bez DPH	Letáková cena v Kč s DPH CZ	Letáková cena v EUR bez DPH	Letáková cena v EUR s DPH SK
92799797	Řídicí jednotka CU 302	14 748,25 Kč	17 845,38 Kč	589,93 €	725,61 €
92817763	Řídicí jednotka CU 302 se snímačem tlaku	19 833,75 Kč	23 998,84 Kč	793,35 €	975,82 €
93176203	Komplet pro udrž. konst. tlaku s SQE 3-65, 40 m kabel, CU302	62 670,75 Kč	75 831,61 Kč	2 506,83 €	3 083,40 €
93176209	Komplet pro udrž. konst. tlaku s SQE 5-70, 40 m kabel, CU302	69 411,50 Kč	83 987,92 Kč	2 776,46 €	3 415,05 €
93176275	Komplet pro udrž. konst. tlaku s SQE 2-55, 40 m kabel, CU302	57 849,25 Kč	69 997,59 Kč	2 313,97 €	2 846,18 €
93176276	Komplet pro udrž. konst. tlaku s SQE 2-85, 60 m kabel, CU302	70 957,00 Kč	85 857,97 Kč	2 838,28 €	3 491,08 €
93187297	Komplet pro udrž. konst. tlaku bez čerpadla	28 733,50 Kč	34 767,54 Kč	1 149,34 €	1 413,69 €
93218720	Komplet pro udrž. konst. tlaku s SQE 2-115, 80 m kabel, CU302	78 198,50 Kč	94 620,19 Kč	3 127,94 €	3 847,37 €
93218784	Komplet pro udrž. konst. tlaku s SQE 3-105, 80 m kabel, CU302	73 794,00 Kč	89 290,74 Kč	2 951,76 €	3 630,66 €
93553163	Komplet pro udrž. konst. tlaku s SQE 3-65, 20 m kabel, CU302	53 844,25 Kč	65 151,54 Kč	2 153,77 €	2 649,14 €
91042982	Sestava lanka z nerez. oceli 20m (pr. 2mm) + 4x úchytky	1 123,90 Kč	1 359,92 Kč	44,96 €	55,30 €
91042984	Sestava lanka z nerez. oceli 30m (pr. 2mm) + 4x úchytky	1 718,56 Kč	2 079,46 Kč	68,74 €	84,55 €
91042986	Sestava lanka z nerez. oceli 50m (pr. 2mm) + 4x úchytky	2 092,81 Kč	2 532,30 Kč	83,71 €	102,97 €
96878506	SEG.40.09.E.2.50B AUTOADAPT 3x400V 50Hz	70 530,71 Kč	85 342,16 Kč	2 821,23 €	3 470,11 €
96878510	SEG.40.12.E.2.50B AUTOADAPT 3x400V 50Hz	70 530,71 Kč	85 342,16 Kč	2 821,23 €	3 470,11 €
96075897	SEG.40.09.2.50B 3x400V 50Hz	46 645,47 Kč	56 441,02 Kč	1 865,82 €	2 294,96 €
96075905	SEG.40.12.2.50B 3x400V 50Hz	46 645,47 Kč	56 441,02 Kč	1 865,82 €	2 294,96 €
96914019	CU 100.400.3.5.A cpl	16 890,09 Kč	20 437,01 Kč	675,60 €	830,99 €
99369644	LC 231 1P DOL	20 256,33 Kč	24 510,16 Kč	810,25 €	996,61 €
99369650	LC 231 2P DOL	25 409,60 Kč	30 745,62 Kč	1 016,38 €	1 250,15 €
96076063	Spouštěcí zař. s aut.spojku DN40 pro SEG	6 774,24 Kč	8 196,83 Kč	270,97 €	333,29 €
96076196	Patky 3ks	3 533,76 Kč	4 275,85 Kč	141,35 €	173,86 €