

SERVICE KIT 1 X 230 - 240 V

MODEL C

Pump type	Pump number	Terminal box	Pump head	Diff. pressure sensor	Adaptor	Gasket set ★
		Pos. Q	Pos. Z	Pos. D	Pos. D1	Pos. N
UPED 32 - 120 F	96 40 31 10	96 40 84 35	96 40 60 51	69 00 50 16	96 41 57 69	96 40 69 40
UPED 40 - 120 F	96 40 31 13	96 40 84 36	96 40 60 52	69 00 50 16	96 41 57 69	96 40 69 40
UPED 50 -60 F	96 40 31 16	96 40 84 37	96 40 60 53	69 00 50 16	96 41 57 69	96 40 69 40
UPED 65 - 60 F	96 40 60 93	96 40 84 38	96 40 60 55	69 00 50 16	96 41 57 69	96 40 69 40

SERVICE KIT 3 X 400 - 415 V

MODEL C

Pump type	Pump number	Terminal box	Pump head	Diff. pressure sensor	Adaptor	Gasket set★
		Pos. Q	Pos. Z	Pos. D	Pos. D1	Pos. N
UPE 50 - 120 F	96 40 21 04	96 40 84 39	96 40 60 54	69 00 50 16		96 40 69 40
UPE 50 - 120 FB	96 40 21 11	96 40 84 39	96 40 60 54	69 00 50 16		96 40 69 40
UPE 65 - 120 F	96 40 22 81	96 40 84 40	96 40 60 56	69 00 50 16		96 40 69 40
UPE 65 - 120 FB	96 40 22 88	96 40 84 40	96 40 60 56	69 00 50 16		96 40 69 40
UPE 80 - 120 F	96 40 24 42	96 40 84 41	96 40 60 57	69 00 50 16		96 40 69 40
UPE 80 - 120 F	96 40 24 43	96 40 84 41	96 40 60 57	69 00 50 16		96 40 69 40
UPE 80 - 120 FB	96 40 58 29	96 40 84 41	96 40 60 57	69 00 50 16		96 40 69 40
UPE 80 - 120 FB	96 40 24 46	96 40 84 41	96 40 60 57	69 00 50 16		96 40 69 40
UPE 100 - 60 F	96 40 26 16	96 40 84 42	96 40 60 58	69 00 50 16		96 40 69 40
UPE 100 - 60 F	96 40 26 18	96 40 84 42	96 40 60 58	69 00 50 16		96 40 69 40
UPE 100 - 60 FB	96 40 58 30	96 40 84 42	96 40 60 58	69 00 50 16		96 40 69 40
UPE 100 - 60 FB	96 40 58 32	96 40 84 42	96 40 60 58	69 00 50 16		96 40 69 40
UPED 50 - 120 F	96 40 31 19	96 40 84 39	96 40 60 54	69 00 50 16	96 41 57 69	96 40 69 40
UPED 65 - 120 F	96 40 31 24	96 40 84 40	96 40 60 56	69 00 50 16	96 41 57 69	96 40 69 40
UPED 80 - 120 F	96 40 31 33	96 40 84 41	96 40 60 57	69 00 50 16	96 41 57 69	96 40 69 40
UPED 80 - 120 F	96 40 31 34	96 40 60 41	96 40 60 57	69 00 50 16	96 41 57 69	96 40 69 40
UPED 100 - 60 F	96 40 58 33	96 40 84 42	96 40 60 58	69 00 50 16	96 41 57 69	96 40 69 40
UPED 100 - 60 F	96 40 58 34	96 40 84 42	96 40 60 58	69 00 50 16	96 41 57 69	96 40 69 40

★) Gasket set for twin heads pumps: use 2 x part number.

SERVICE KIT 1 X 230 - 240 V

MODEL A AND B

Pump type	Pump number	Terminal box	Pump head
		Pos. Q	Pos. Z
UPE 32 - 120 F	96 40 18 40	60 55 77	54 31 48 47
	96 41 54 94 ★		
UPE 32 - 120 FB	96 40 18 47		
UPE 40 - 120 F	96 40 19 45	60 55 78	54 41 48 47
	96 41 54 95 ★		
UPE 40 - 120 FB	96 40 19 52		
UPE 50 -60 F	96 40 20 56	60 55 79	54 51 47 47
	96 41 54 96 ★		
UPE 50 -60 FB	96 40 20 75		
UPE 65 - 60 F	96 40 22 61	60 55 80	54 61 47 47
	96 41 54 97 ★		
UPE 65 - 60 FB	96 40 22 65		

★ Northern Europe.

