






L-leder i eksempel under er koblet via automatikkskapets potensialfrie releutgang for alarm høyt nivå.





Alarm boks med summer 230VAC

Pos.	Varenr:		Betegnelse	Type	Fabrikant
P1	0775-7850320	1	Lampe Rød	800F-BN7 230V AC	AB
S1	0775-7850177	1	Bryter	800F-BX01 NC	AB
	0775-7880389	1	Lampetryk Rød m/kip plan	800FP-L.FA4	AB
	0810-7849799	1	Boks	800F-2PM	AB
P2	0775-7906195	1	Summer	855P-B20SE22 230V AC	AB
	0839-5308941	1	Kabelforskruning	M16 sort	
	0839-2002304	1	Kabelforskrunings møttrik	M16 sort	
	0838-0001458	1	Ledning S1:1 - P1:X1	0,5mm ² sort	
	0838-0001459	1	Ledning S1:2 - P2:La	0,5mm ² sort	
	0838-0001460	1	Ledning P1:X2 - P2:N	0,5mm ² sort	
	0900-1190026	1	Label 27x18 sort		



Alternativ løsning her med nivåvippe SLC10E 96061654 nrfnr 9045636.
HØYT NIVÅ ALARM via vippe direkte inn på alarmboks.
Vippens ledning nr 1 og 2 kobles til her, ledning nr 3 isoleres.



Alarm boks med summer 230VAC

Pos.	Varenr:		Betegnelse	Type	Fabrikant
P1	0775-7850320	1	Lampe Rød	800F-BN7 230V AC	AB
S1	0775-7850177	1	Bryter	800F-BX01 NC	AB
	0775-7880389	1	Lampetryk Rød m/kip plan	800FP-L.FA4	AB
	0810-7849799	1	Boks	800F-2PM	AB
P2	0775-7906195	1	Summer	855P-B20SE22 230V AC	AB
	0839-5308941	1	Kabelforskruning	M16 sort	
	0839-2002304	1	Kabelforskrunings møttrik	M16 sort	
	0838-0001458	1	Ledning S1:1 - P1:X1	0,5mm ² sort	
	0838-0001459	1	Ledning S1:2 - P2:La	0,5mm ² sort	
	0838-0001460	1	Ledning P1:X2 - P2:N	0,5mm ² sort	
	0900-1190026	1	Label 27x18 sort		



Grundfos A/S

ALARM BOKS MED SUMMER 230VAC

Proj. no.: 98362986	Rev.: 16-10-2012	Item Des.	Page: 1
Date: 24-04-2012	Doc. no.:	Ver.: 01	Created by: NF Next Page: